

Rittal – The System.

Faster – better – everywhere.



DK 7507.210

FlatBox

State: 2/14/2026 (Source: ittal.com/us-en)



FRIEDHELM LOH GROUP

DK 7507.210 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.



Features

| | |
|---------------------|--|
| Model No. | DK 7507.210 |
| Version | with 19" mounting frame |
| Product description | For flexible use as a wall-mounted or floor-standing enclosure. |
| Benefits | Tool-free quick mounting System accessories on the open 19" frame |
| Material | Carbon steel Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Color | RAL 7035 |

Features

| | |
|-------------------------------------|---|
| Supply includes | Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts 19" mounting frame |
| Height units | 18 U |
| Dimensions | Width: 700 mm Height: 892 mm Depth: 700 mm Width: 27.6 " Height: 35.1 " Depth: 27.6 " |
| Installation height for components | 18 U |
| Load capacity | max. 750 N |
| Note | Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210° |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Net weight | 45.6 |
| Gross weight | 48.4 |
| PCF/VE (cradle-to-gate) | 182.9 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94032080 |
| EAN | 4028177551473 |
| E-Number Sweden | E7238407 |

Features

ETIM 9 EC002500

ETIM 8 EC002500

ECLASS 8.0 27180208

Approvals

Explanations

Manufacturer's declaration