

Rittal – The System.

Faster – better – everywhere.



DK 7715.735

Wall-mounted enclosures EL, 3-part

State: 7/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7715.735 - Wall-mounted enclosures EL, 3-part pre-configured with profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, ground rail, wall-mounting bracket

Features

| | |
|---------------------|---|
| Model No. | DK 7715.735 |
| Version | Wall-mounted housing IT pre-configured with profile rails, depth-variable |
| Product description | Wall-mounted enclosure with hinged door provides optimum accessibility. |
| Material | Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| General color | RAL 7035 |
| Color | Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray) |
| Supply includes | Wall section with solid gland plate at the top and brush strip at the bottom, two vertical mounting rails and C rail, horizontal, for cable clamping Hinged part with 25 mm pitch pattern in the front and rear frame, two 482.6 mm (19") profile angles at the front, fully depth adjustable and side outlet filters on left and right Ground rail with star grounding Designer viewing door 1 enclosure key double bit no. 5 Wall mounting brackets, 10 mm Mini-comfort handle for lock inserts Security lock 3524 E |
| Height units | 15 U |

Features

| | |
|---------------------------------------|--|
| Dimensions | Width: 600 mm Height: 746 mm Depth: 573 mm Width: 23.6 " Height: 29.4 " Depth: 22.6 " |
| Installation depth | 520 mm 20.5 " |
| Clearances | Clearance width: 502 mm Clearance height: 683 mm Clearance width: 19.8 " Clearance height: 26.9 " |
| Depth hinged part | 416 mm 16.4 " |
| Depth of wall section | 135 mm 5.31 " |
| IK code | IK08 |
| Load capacity of hinged part (static) | 750 N 168.607 lbf. |
| Base material | Carbon steel |
| Protection category IP to EN 60529 | IP 54 in conjunction with solid gland plate top and bottom |
| Packaging unit | 1 pc(s). |
| Net weight | 42.75 kg |
| Gross weight | 45 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27142408 |
| Product description | DK wall-mounted enclosure, 3-part, WHD: 600x746x573 mm, 15 HE, pre-mounted, IP 54 with closed flange plate at top and bottom |

Approvals

Approvals

UL + C-UL (listed)