

# Rittal – The System.

Faster – better – everywhere.



## DK 7715.735

# Wall-mounted enclosures EL, 3-part

State: 1/16/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7715.735 - Wall-mounted enclosures EL, 3-part pre-configured with profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, ground rail, wall-mounting bracket

## Features

Model No.	DK 7715.735
Version	Wall-mounted housing IT pre-configured with profile rails, depth-variable
Product description	Wall-mounted enclosure with hinged door provides optimum accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section with solid gland plate at the top and brush strip at the bottom, two vertical mounting rails and C rail, horizontal, for cable clamping Hinged part with 25 mm pitch pattern in the front and rear frame, two 482.6 mm (19") profile angles at the front, fully depth adjustable and side outlet filters on left and right Ground rail with star grounding Designer viewing door 1 enclosure key double bit no. 5 Wall mounting brackets, 10 mm Mini-comfort handle for lock inserts Security lock 3524 E
Height units	15 U

# Features

---

Dimensions	Width: 600 mm Height: 746 mm Depth: 573 mm Width: 23.6 " Height: 29.4 " Depth: 22.6 "
Installation depth	520 mm 20.5 "
Clearances	Clearance width: 502 mm Clearance height: 683 mm Clearance width: 19.8 " Clearance height: 26.9 "
Depth hinged part	416 mm 16.4 "
Depth of wall section	135 mm 5.31 "
IK code	IK08
Load capacity of hinged part (static)	750 N 168.607 lbf.
Base material	Carbon steel
Protection category IP to EN 60 529	IP 54 in conjunction with solid gland plate top and bottom
Packaging unit	1 pc(s).
Net weight	42.75
Gross weight	45
Customs tariff number	94032080
EAN	4028177324244
E-Number Sweden	E7239959
ETIM 9	EC000261
ECLASS 8.0	27142408

# Approvals

---

Approvals

UL + C-UL (listed)