

Rittal – The System.

Faster – better – everywhere.



DK 7816.362

Carbon steel door, vertically divided,
closed

State: 12/20/2025 (Source: [m/us-en](#))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7816.362 - Carbon steel door, vertically divided, closed for DK-TS

To replace existing doors. The minimal pivoting radius of the individual doors allows the distance between individual bayed enclosure suites to be reduced.

Features

Model No.	DK 7816.362
Product description	With 130° hinges and locking rod, including comfort handle for semi-cylinder with security lock no. 3524 E. Due to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.
Material	Carbon steel
Supply includes	Assembly components
Note on Model No.:	Without tubular door frame. Tubular door frame available on request.
Protection category IP to IEC 60529	IP 55
Suitable for	Enclosure type: DK-TS Width: 600 mm Height: 2,200 mm Enclosure type: DK-TS Width: 23.6 " Height: 86.6 "
Packaging unit	1 pc(s).
Net weight	28.69
Gross weight	30.2
Customs tariff number	94032080
EAN	4028177330504
ECLASS 8.0	27182204