

Rittal – The System.

Faster – better – everywhere.



TS 7825.367

Base modules for cable entry

State: 5/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 7825.367 - Base modules for cable entry for TS, TS IT, VX SE

The two-part base module has a special cable entry with alternate offset brush strips, providing an excellent seal even with large numbers of cables.



Features

| | |
|---------------------|--|
| Model No. | TS 7825.367 |
| Version | Cable entry with brush strip, super-airtight |
| Product description | Special brush strips with alternate offset brushes for optimum protection of correct cable entry. The two-piece design even allows retrospective fitting of the base module with the cables already installed. |
| Material | Module plate: Carbon steel Brush strip: Plastic, UL 94-HB, halogen-free |
| Surface finish | Module plate: Zinc-plated |
| Supply includes | Assembly components Including clips |
| Note | Several base plate modules need to be combined to close off the base completely in the TS-IT |
| Dimensions | Depth: 237.5 mm Depth: 9.35 " |

Features

| | |
|-----------------------|--|
| Suitable for | Enclosure type: TS TS IT SE Width: 600 mm Enclosure type: TS TS IT SE Width: 23.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 1.3 kg |
| Gross weight | 1.42 kg |
| Customs tariff number | 83024200 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Gland plate module, For W: 600 mm, For cable entry with brush, super-airtight |