


Rittal – The System.

Faster – better – everywhere.



DK 7856.082

PSM Outlet Modules

State: 2/10/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7856.082 - PSM Outlet Modules

The various modules and ground contacts can be inserted into the support rail in any combination.

Features

Model No.	DK 7856.082
Version	non-switchable
Product description	The modular system enables basic configuration of the racks using a vertical support rail with single/three-phase infeed. The different socket modules can be snapped into position in the support rail to supply the active components. The various modules, ground contacts and IEC320 can be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system.
Material	Profile: Aluminum, anodized Socket inserts: Plastic (PA6 GF 30 V1)
Length	250 mm 9.84 "
Type of connection (electrical)	WAGO WINSTA MIDI
Phases per infeed	1~
Thermal overcurrent protection	–
Rated operating voltage	110 V – 230 V AC, 50/60 Hz
Rated current (max.)	16 A
Required module slots (quantity)	1
Dimensions	Length: 250 mm Length: 9.84 "
Operating temperature range	5 °C...45 °C 41 °F...113 °F
Ambient humidity (non-condensing)	5...95 %
Outlets	6 x Non-Heating Apparatus Socket C13, Red

Features

Packaging unit 1 pc(s).

Net weight 0.33

Gross weight 0.338

Customs tariff number 85369001

EAN 4028177520318

ETIM 9 EC000330

ECLASS 8.0 27142604

Approvals

Approvals IEC CB
VDE

Explanations Declaration of conformity