

Rittal – The System.

Faster – better – everywhere.



CP 6148.000 Twin castors

State: 6/22/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6148.000 - Twin castors

For mobile use, can be mounted directly on the enclosure.

Features

Model No.	CP 6148.000
Product description	For mobile use, can be mounted directly on the enclosure.
Color	Black with gray running surface
Supply includes	4 twin castors, 2 x with, 2 x without locks. Assembly components
Suitable for	Enclosure type: VX Enclosure type: VX IT Enclosure type: TS Enclosure type: TS IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller
Clearande floor	85 mm 3.35 "
Max. load capacity (static) per component	750 N 168.607 lbf.
Suitable for Model No.	6106.200 6106.300
Dimensions	Thread: M12 x 20
Packaging unit	1 pc(s).
Net weight	1.115 kg
Gross weight	1.293 kg
Customs tariff number	39269097
ETIM 9	EC002621

Features

ECLASS 8.0

27189262

Product description

CP Twin castors, 2 each with/without lock, static load per castor 75 kg