

# Rittal – The System.

Faster – better – everywhere.



## TE 7888.390

## Network enclosure TE 8000

State: 6/21/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7888.390 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

## Features

Model No.	TE 7888.390
Version	with side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E
Dimensions	Width: 600 mm Height: 600 mm Depth: 600 mm Width: 23.6 " Height: 23.6 " Depth: 23.6 "

# Features

Height units	11 U
Height units	11 U
Mounting space to 19" level, front/ rear	30 mm / 30 mm /
Distance between levels as delivered	495 mm 19.5 ~
Load capacity	4,000 N
Protection category IP to EN 60 529	IP 20
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	35
Gross weight	36.06
EAN	4028177801387
E-Number Sweden	E7239994
ETIM 9	EC002499
ECLASS 8.0	27180207

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------