

Rittal – The System.

Faster – better – everywhere.



TE 7888.520

Network enclosure TE 8000

State: 6/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7888.520 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

Features

Model No.	TE 7888.520
Version	with side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 600 mm Width: 31.5 " Height: 78.7 " Depth: 23.6 "

Features

Height units	42 U
Height units	42 U
Mounting space to 19" level, front/ rear	30 mm / 30 mm /
Distance between levels as delivered	495 mm 19.5 "
Load capacity	4,000 N
Protection category IP to EN 60 529	IP 20
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	100 kg
Gross weight	103 kg
Customs tariff number	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Product description	TE Network enclosure TE 8000, WHD: 800x2000x600 mm, 42 U, With glazed door

Approvals

Explanations	Declaration of conformity
--------------	---------------------------