

# Rittal – The System.

Faster – better – everywhere.



## CP 6206.460

## Tilting adapter $+100^{\circ}/-60^{\circ}$

State: 8/1/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6206.460 - Tilting adapter +100°/–60° for support arm connection 120 x 65 mm

Mounted on IW worktop, prepared for Ø 130 mm attachment, surfaces or attachments/couplings with 120 x 65 mm support arm connection. To fit housings up to 20 kg with support arm connection. With cable tube for protected cable entry.

## Features

Model No.	CP 6206.460
Version	For mounting on IW worktop, prepared for attachment of 130 mm diameter Surfaces For attachment/coupling with 120 x 65 mm support arm connection Suitable for enclosures up to 20 kg with support arm connection 90 x 71 mm Ø 130 mm 120 x 65 mm VESA Standard 75 With cable tube for protected cable entry.
Product description	Tilting angle adjustable in 7.2° increments using clamping lever and may be limited to +100°/–15° using the stop screw supplied loose.
Material	Tilting adapter: Carbon steel, spray finished Concertina section: Plastic
Color	Tilting adapter: RAL 7035 Concertina section: RAL 7024
Supply includes	Assembly components Concertina section
Rotating/tilting	Yes
Tilt angle note	Adjustable in 7.2° increments via clamping lever and may be limited to +100°/–15° using the stop screw supplied loose
Packaging unit	1 pc(s).
Net weight	0.86
Gross weight	0.871

# Features

PCF/VE (cradle-to-gate)	3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177684454
ETIM 9	EC000882
ECLASS 8.0	27400556

# Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------