

# Rittal – The System.

Faster – better – everywhere.



## TE 7888.532

## Network enclosure TE 8000

State: 8/1/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7888.532 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

## Features

Model No.	TE 7888.532
Version	without side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Baying kit
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 "

# Features

Height units	42 U
Height units	42 U
Mounting space to 19" level, front/ rear	130 mm / 130 mm /
Distance between levels as delivered	495 mm 19.5 ~
Load capacity	4,000 N
Protection category IP to EN 60 529	IP 20
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	90.25
Gross weight	93
EAN	4028177801479
E-Number Sweden	E7282503
ETIM 9	EC002499
ECLASS 8.0	27180207

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------