

# Rittal – The System.

Faster – better – everywhere.



## CP 6320.500

## Operating housing with handle strips

State: 12/15/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6320.500 - Operating housing with handle strips

Command panel with handle strips in contemporary design of sheet steel, with Ø 130 mm support arm cut-out to fit CP 60/120/180 support arm system, service access optionally from the front or rear, aluminum front panel easily removable for machining, protection category IP 55



## Features

Model No.	CP 6320.500
Material	Housing and door: Carbon steel Handle strips: Aluminum Front panel: Aluminum Cover caps: Plastic
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Handle strip: Natural anodized Front panel: Natural anodized.
Color	Housing and door: RAL 7035 Handle strip: Natural anodized Front panel: Natural anodized. Cover caps: Similar to RAL 7024
Supply includes	Housing with cut-out and reinforcement for support arm connection Ø 130 mm Front with maximum cut-out, covered with easily machinable 3 mm aluminum front panel Side handle strips and cover caps Cam lock with 3 mm double-bit insert Integral interior mounting bracket with TS system punchings

# Features

Dimensions	Width: 600 mm Height: 380 mm Depth: 210 mm Width: 23.6 " Height: 15 " Depth: 8.27 "
Protection category IP to IEC 60529	IP 55
Version	Service access from rear
Note	The support arm connection and door catch may be swapped over by rotating the enclosure Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out Lock systems for servicing access from the rear: 27 mm lock inserts, type A, lock cylinder, plastic handles and T-handles, type B
Base material	Aluminum
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	12.586
Gross weight	13.248
Customs tariff number	94032080
EAN	4028177694002
ECLASS 8.0	27180505

## Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---