Rittal – The System.

Faster - better - everywhere.





CP 6372.553 Comfort Panel

State: 11/4/2025 (Source: rittal.com/us-en)



CP 6372.553 - Comfort Panel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability. Protection category IP 65 to IEC 60 529.







Features

Model No.	CP 6372.553
Version	Support arm connection Ø 130 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability
	Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section
	Corner pieces: Die-cast zinc
	Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized.
	Corner pieces: RAL 7035
	Corner protectors: Similar to RAL 7024
Supply includes	Enclosure with cut-out for support arm connection
	3 mm double-bit lock insert may be exchanged for 41 mm lock
	inserts, plastic handles and T handles, type C
	Seals and assembly components for front panels
	Rear panel screwed, enclosure hinged at the front with side double-
	bit lock insert

© Rittal 2025 2

Features

Dimensions	Width: 628.5 mm
	Height: 608.5 mm
	Depth: 209 mm
	Width: 24.7 "
	Height: 24 "
	Depth: 8.23 "
Installation depth	191 mm
	7.52 ″
Protection category IP to IEC 60 529	IP 65
Protection category NEMA	NEMA 12
	INEIVIA 12
Suitable for front panel width	520 mm
	20.5 ″
Suitable for front panel height	500 mm
	19.7 ″
Version	Service access from rear
Note	The support arm connection may be swapped over by rotating the
	enclosure
Base material	Aluminum
Lock	Lock version: Sickle-shaped locking nose
	No. of locks: 2
	Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	17
Gross weight	18.1
EAN	4028177663114
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

© Rittal 2025 3

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025