

# Rittal – The System.

Faster – better – everywhere.



## CP 6380.000

## Optipanel

State: 1/31/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



FRIEDHELM LOH GROUP

# CP 6380.000 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.



## Features

Model No.	CP 6380.000
Version	Support arm connection, rectangular 120 x 65 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024
Supply includes	Housing with hinged rear panel Seals

# Features

Dimensions	Width: 526.6 mm Height: 354.3 mm Depth: 110 mm Width: 20.7 " Height: 13.9 " Depth: 4.33 "
Installation depth	100 mm 3.94 "
Protection category IP to IEC 60 529	IP 65
Suitable for front panel width	482.6 mm 19 "
Suitable for front panel height	310.3 mm 12.2 "
Version	Service access from rear
Note	The support arm connection may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Rear panel hinges on the longest enclosure side
Base material	Aluminum
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	5.86
Gross weight	6.168
Customs tariff number	94032080
EAN	4028177231627
ETIM 9	EC002504
ECLASS 8.0	27180505

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK