

Rittal – The System.

Faster – better – everywhere.



CP 6380.020

Optipanel

State: 6/19/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6380.020 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.



Features

| | |
|-----------------|---|
| Model No. | CP 6380.020 |
| Version | Support arm connection, rectangular 120 x 65 mm |
| Benefits | Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems |
| Material | Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic |
| General color | Natural anodized |
| Color | Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024 |
| Supply includes | Housing with hinged rear panel Seals |

Features

| | |
|-------------------------------------|---|
| Dimensions | Width: 474 mm Height: 387 mm Depth: 110 mm Width: 18.7 " Height: 15.2 " Depth: 4.33 " |
| Installation depth | 100 mm 3.94 " |
| Protection category IP to IEC 60529 | IP 65 |
| Suitable for front panel width | 430 mm 16.9 " |
| Suitable for front panel height | 343 mm 13.5 " |
| Version | Service access from rear |
| Note | The support arm connection may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Rear panel hinges on the longest enclosure side |
| Base material | Aluminum |
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit |
| Packaging unit | 1 pc(s). |
| Net weight | 5.898 kg |
| Gross weight | 6.208 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002504 |
| ECLASS 8.0 | 27180505 |
| Product description | CP Optipanel, for front panel BH 430x343 mm, installation depth 100 mm, Extruded aluminum section, Support arm connection 120x65 mm |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
