


Rittal – The System.

Faster – better – everywhere.



CP 6380.040 Optipanel

State: 9/2/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6380.040 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.



Features

Model No.	CP 6380.040
Version	Support arm connection, rectangular 120 x 65 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024
Supply includes	Housing with hinged rear panel Seals

Features

Dimensions	Width: 526.6 mm Height: 398.8 mm Depth: 110 mm Width: 20.7 " Height: 15.7 " Depth: 4.33 "
Installation depth	100 mm 3.94 "
Protection category IP to IEC 60529	IP 65
Suitable for front panel width	482.6 mm 19 "
Suitable for front panel height	354.8 mm 14 "
Version	Service access from rear
Note	The support arm connection may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Rear panel hinges on the longest enclosure side
Base material	Aluminum
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	6.069
Gross weight	6.388
EAN	4028177429093
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK