


Rittal – The System.

Faster – better – everywhere.



CP 6380.510 Optipanel

State: 6/29/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6380.510 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.



Features

| | |
|--------------------|---|
| Model No. | CP 6380.510 |
| Version | Support arm connection Ø 130 mm |
| Benefits | Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems |
| Material | Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic |
| General color | Natural anodized |
| Color | Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024 |
| Supply includes | Housing with hinged rear panel Seals Seals and assembly components for front panels |
| Installation depth | 150 mm 5.91 " |

Features

| | |
|-------------------------------------|---|
| Protection category IP to IEC 60529 | IP 65 |
| Suitable for front panel width | 520 mm 20.5 " |
| Suitable for front panel height | 500 mm 19.7 " |
| Version | From the rear |
| Note | The support arm connection may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Rear panel hinges on the longest enclosure side |
| Base material | Aluminum |
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit |
| Packaging unit | 1 pc(s). |
| Net weight | 10.922 |
| Gross weight | 11.497 |
| Customs tariff number | 94032080 |
| EAN | 4028177663183 |
| ETIM 9 | EC002504 |
| ECLASS 8.0 | 27180505 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |