

**Rittal – The System.**

Faster – better – everywhere.



**WM 8017.582**

**WM wall-mounted enclosure**

State: 12/18/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8017.582 - WM wall-mounted enclosure double door

These double door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.

## Features

Model No.	WM 8017.582
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Dipcoat-primed and powder-coated, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Mounting plate Rear wall mounting holes
Dimensions	Width: 1,050 mm Height: 900 mm Depth: 300 mm Width: 41.3 " Height: 35.4 " Depth: 11.8 "
Dimensions of mounting plate (W x H)	1,000 mm x 850 mm 39.4 " x 33.5 "
Protection category NEMA	NEMA 12 NEMA 12
Material thickness - door	2 mm 0.08 "
Material thickness - enclosure	2 mm 0.08 "
Material thickness – mounting plate	2.5 mm 0.1 "

# Features

3-point locking system	Yes
Number of doors	2
Packaging unit	1 pc(s).
Net weight	147.994
Gross weight	147.994
Customs tariff number	8538100000
UPC-Code	83159

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity