Rittal - The System.

Faster – better – everywhere.





SM 6450.020 TFT monitor

State: 11/17/2025 (Source: rittal.com/us-en)



SM 6450.020 - TFT monitor

Mounting variant for surfaces and command panels.

Features

Model No.	SM 6450.020		
Version	Without touchscreen		
Product description	Mounting variant for surfaces and command panels.		
Benefits	High-quality industrial design		
	Reduced installation work thanks to integral front frame		
	No additional ventilation required		
	Very small installation depth (45 mm)		
Material	Front frame: Aluminum		
Surface finish	Powder-coated		
Color	RAL 7035		
Supply includes	Seal		
	Hex nuts (for installation in surfaces)		
	VGA cable		
	Threaded bolt M5, for rear mounting		
	Touch variants additionally with integrated connection cable and		
	CD-ROM driver		
	With anti-reflection coated safety glass screen.		
Dimensions	Width: 482.6 mm		
	Height: 354.8 mm		
	Width: 19 "		
	Height: 14 "		
Interfaces	VGA (D-SUB HD 15-pole)		
	DVI-D		
Operating temperature range	0 °C50 °C		
	32 °F122 °F		
Storage temperature range	-30 °C85 °C		
	-22 °F185 °F		

© Rittal 2025

Features

Note on Model No.:	Other variants as resistive touchscreen with serial or USB interface available on request.	
Display brightness	350 cd/m²	
Contrast ratio	1000 : 1	
Diagonal	17"	
Operating time	50,000 h	
On Screen Display (OSD)	Operating buttons at the rear	
Reading angle left/right	85 °	
Display resolution	1280 x 1024 pixels	
Rated power Pel	with DC: 20 W	
H-Sync. (min./max.)	31.4 - 80 kHz	
V-Sync. (min./max.)	60 - 75 Hz	
Number of colors	16.7	
Resolution of controller	VGA SVGA XGA SXGA	
Packaging unit	1 pc(s).	
Net weight	6.897	
Gross weight	7.26	
Customs tariff number	85286200	
EAN	4028177442429	
ETIM 9	EC001428	
ECLASS 8.0	19200201	

Approvals

	Explanations	Declaration of conformity	
--	--------------	---------------------------	--

© Rittal 2025 3