Rittal - The System.

Faster – better – everywhere.





SM 6450.170 TFT monitor

State: 11/19/2025 (Source: rittal.com/us-en)



SM 6450.170 - TFT monitor

Mounting variant for surfaces and command panels.

Features

Model No.	SM 6450.170
Version	Without touchscreen
Product description	Mounting variant for surfaces and command panels.
Benefits	High-quality industrial design
	Reduced installation work thanks to integral front frame
	No additional ventilation required
	Very small installation depth (45 mm)
Material	Front frame: Aluminum
Surface finish	Powder-coated
Color	RAL 7035
Supply includes	Seal
	Hex nuts (for installation in surfaces)
	VGA cable
	Threaded bolt M5, for rear mounting
	Touch variants additionally with integrated connection cable and
	CD-ROM driver
	With anti-reflection coated safety glass screen.
Dimensions	Width: 482.6 mm
	Height: 399.3 mm
	Width: 19 "
	Height: 15.7 "
Interfaces	VGA (D-SUB HD 15-pole)
	DVI-D
Operating temperature range	0 °C50 °C
	32 °F122 °F
Storage temperature range	-20 °C60 °C
	-4 °F140 °F

© Rittal 2025

Features

Note on Model No.:	Other variants as resistive touchscreen with serial or USB interface available on request.
Display brightness	350 cd/m²
Contrast ratio	1000 : 1
Diagonal	19"
Operating time	50,000 h
On Screen Display (OSD)	Operating buttons at the rear
Reading angle left/right	85°
Display resolution	1280 x 1024 pixels
Note on Model No.:	With anti-reflection coated safety glass screen.
Rated power Pel	with DC: 20 W
H-Sync. (min./max.)	31.5 - 80 kHz
V-Sync. (min./max.)	60 - 75 Hz
Number of colors	16.7
Resolution of controller	VGA SVGA XGA SXGA
Packaging unit	1 pc(s).
Net weight	7.6
Gross weight	8
Customs tariff number	85286200
EAN	4028177511613
ETIM 9	EC001428
ECLASS 8.0	19200201

Approvals

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

© Rittal 2025