

Rittal – The System.

Faster – better – everywhere.



WM 8017.592

WM wall-mounted disconnect enclosure

State: 4/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.592 - WM wall-mounted disconnect enclosure

These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.

Features

Model No.	WM 8017.592
Product description	These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.
Material	Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel, zinc-plated
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Flange door with universal disconnect cutout
Dimensions	Width: 975 mm Height: 1,500 mm Depth: 300 mm Width: 38.4 " Height: 59.1 " Depth: 11.8 "
Dimensions of mounting plate (W x H)	840 mm x 1,455 mm 33.1 " x 57.3 "
Protection category NEMA	NEMA 4 UL Type 4/3R/12

Features

Material thickness - door	2 mm 0.08 "
Material thickness - enclosure	2 mm 0.08 "
Material thickness – mounting plate	3 mm 0.12 "
Packaging unit	1 Pair
Net weight	218.997 lb
Gross weight	218.997 lb
Customs tariff number	8538100000

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
