

Rittal – The System.

Faster – better – everywhere.



CX 6704.000

CX Pedestal

State: 6/12/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6704.000 - CX Pedestal

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



Features

Model No.	CX 6704.000
Version	Pedestal
Material	Housing: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Carbon steel, 2.5 mm
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing open at top Door or double door at front, with 3-point locking system Mounting panel Base Plates Lock: 3 mm double-bit

Features

Dimensions	Width: 600 mm Height: 675 mm Depth: 500 mm Width: 23.6 " Height: 26.6 " Depth: 19.7 "
Dimensions of mounting plate (W x H)	520 mm x 625 mm 20.5 " x 24.6 "
Number of doors	1
Door opening angle	130°
IK code	IK10
Note	To close the pedestal, a closure plate is required For a 2-piece console setup, a desk unit and a closure plate for the desk unit are required For a 3-piece console setup, a desk unit and console top-section are required
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Base material	Carbon steel
No. of locks	1
Lock version	3-point locking system
Lock Insert	3 mm double-bit
Lock	Lock version: 3-point locking system No. of locks: 1 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	34 kg
Gross weight	35.75 kg
Customs tariff number	94032080
ETIM 9	EC000784

Features

ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	CX console system, pedestal, WHD: 600x675x500 mm, carbon steel

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity