Rittal – The System.

Faster – better – everywhere.



WM 8017.596

WM wall-mounted disconnect enclosure

State: 11/10/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WM 8017.596 - WM wall-mounted disconnect enclosure

These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.596
Product description	These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.
Material	Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel, zinc-plated
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Flange door with universal disconnect cutout 3-point latching L-Handle

Features

Dimensions	Width: 975 mm Height: 1,200 mm Depth: 400 mm Width: 38.4 ″ Height: 47.2 ″ Depth: 15.7 ″
Dimensions of mounting plate (W x H)	840 mm x 1,155 mm 33.1 ″ x 45.5 ″
Protection category NEMA	NEMA 4 UL Type 4/3R/12
Material thickness - door	2 mm 0.08 ″
Material thickness - enclosure	2 mm 0.08 ″
Material thickness – mounting plate	3 mm 0.12 ″
Packaging unit	1 pc(s).
Net weight	211.64 lb
Gross weight	212 lb
Customs tariff number	8538100000

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity