

# Rittal – The System.

Faster – better – everywhere.



## DK 7010.220 Sensors

State: 6/11/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7010.220 - Sensors for CMC III, PDU, LCP, IoT interface

The leak sensor monitors the base for conductive liquids (leakage) using a 15-meter long sensor cable.

## Features

Model No.	DK 7010.220
Version	Leakage sensor for cabinet rows
Benefits	Fast connection and automatic detection via plug & play Power is supplied via the CAN bus interface.
Applications	Enclosure monitoring in IT, industry and facility management Monitoring enclosures, rooms and containers in the field of IT.
Function principle	Settings can be made via the CMC III Processing Unit, the PDU or via the IoT interface The 15 m long sensor cable is attached securely to the base. If the sensor cable comes into contact with a conductive liquid, the sensor will report a leak
Material	Plastic
Surface finish	Front: Smooth Housing: Textured
Color	RAL 9005
Supply includes	Leak sensor Detection cable, 15 m Mounting panel Assembly components
Connection to the CAN bus	Direct
Interfaces	2 x RJ45 CAN bus
Dimensions	Width: 110 mm Height: 30 mm Depth: 40 mm Width: 4.33 " Height: 1.18 " Depth: 1.57 "

# Features

---

Operating temperature range	0 °C...45 °C 32 °F...113 °F
Ambient humidity (non-condensing)	5...95 %
Packaging unit	1 pc(s).
Net weight	0.85 kg
Gross weight	1.057 kg
Customs tariff number	90261029
ETIM 9	EC002627
Product description	DK leakage sensor, for cabinet rows, connection via CAN bus interface, W x H x D: 110 x 30 x 40 mm, RAL 9005

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity