

# Rittal – The System.

Faster – better – everywhere.



## DK 7030.501

## Door control module

State: 6/7/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7030.501 - Door control module

Control unit for automatic opening of VX IT glazed doors for ADO with integrated vent flaps.

## Features

Model No.	DK 7030.501
Product description	Control unit for automatic opening of VX IT glazed doors for ADO with integrated vent flaps. Designed for a rack with a front and rear door. Suitable for the CMC III system with CAN bus.
Technical specifications	<p>Maximum number of PU: 16</p> <p>Maximum number of PU Compact: 4</p> <p>1. Rated voltage: 24 V (DC) 7030.060 for door control module and VX IT glazed doors for ADO, redundant to the second Rated voltage</p> <p>2. Rated voltage: 24 V (DC) 7030.060 for Door Control Module and VX IT glazed doors for ADO</p> <p>1 x Temperature sensor input</p> <p>3 x digital inputs: Alarm/front door flaps/rear door flaps</p> <p>1 x input for readers: Numerical coded lock/transponder reader for on-site function test of the ventilation flaps</p> <p>2 x outlets for VX IT glazed doors for ADO with integrated ventilation flaps, magnet system with damper integrated in the door</p> <p>2 x CAN bus CMC III: RJ45 for CAN bus cables</p>
Material	Plastic
Color	Front: RAL 9005 Housing: RAL 7035
Supply includes	<p>Basic system</p> <p>Temperature sensor including connection cable (supplied loose)</p> <p>Incl. assembly parts for mounting on surfaces</p>
Packaging unit	1 pc(s).
Net weight	0.4
Gross weight	0.66
Customs tariff number	90330090
EAN	4028177951570

# Features

ETIM 9	EC001770
ECLASS 8.0	27390190

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity