



Rittal – The System.

Faster – better – everywhere.



DK 7396.000

Data Rack

State: 7/14/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7396.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation, and a high degree of mobility when twin castors are used.



Features

Model No.	DK 7396.000
Material	Profile frame, base/plinth: Carbon steel Feet: Die-cast zinc
General color	RAL 7035
Color	Profile frame, base/plinth: RAL 7035 Panel, feet: RAL 5018
Supply includes	Torsionally rigid profile frame with 482.6 mm (19") holes Stable base/plinth with integral feet, with the option of floor anchoring without base trim panels Mounting Accessories
Dimensions	Width: 550 mm Height: 1,722 mm Depth: 750 mm Width: 21.7 " Height: 67.8 " Depth: 29.5 "
Height units	36 U
Height units	36 U

Features

Distance from the second mounting level, 50 mm hole pattern	150 - 350 mm 5.91 - 13.8 "
Hole pattern between the mounting levels	50 mm 1.97 "
Load capacity of the 19" levels	1,500 N
Note	Order second mounting level separately
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	15.1
Gross weight	18.5
PCF/VE (cradle-to-gate)	71.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177129894
E-Number Sweden	E7239647
ETIM 9	EC002507
ECLASS 8.0	27180602