Rittal - The System.

Faster - better - everywhere.






State: 12/10/2025 (Source: rittal.com/us-en)



DK 7396.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation, and a high degree of mobility when twin castors are used.







Features

Model No.	DK 7396.000
Material	Profile frame, base/plinth: Carbon steel
	Feet: Die-cast zinc
General color	RAL 7035
Color	Profile frame, base/plinth: RAL 7035
	Panel, feet: RAL 5018
Supply includes	Torsionally rigid profile frame with 482.6 mm (19") holes
	Stable base/plinth with integral feet, with the option of floor
	anchoring without base trim panels
	Mounting Accessories
Dimensions	Width: 550 mm
	Height: 1,722 mm
	Depth: 750 mm
	Width: 21.7 "
	Height: 67.8 "
	Depth: 29.5 "
Height units	36 U
Height units	36 U

© Rittal 2025

Features

Distance from the second	150 - 350 mm
mounting level, 50 mm hole	5.91 - 13.8 <i>"</i>
pattern	
Hole pattern between the	50 mm
mounting levels	1.97 ″
Load capacity of the 19" levels	1,500 N
Note	Order second mounting level separately
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	15.1
Gross weight	18.5
PCF/VE (cradle-to-gate)	71.1 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177129894
E-Number Sweden	E7239647
ETIM 9	EC002507
ECLASS 8.0	27180602

© Rittal 2025 3