Rittal – The System.

Faster – better – everywhere.



CP 7495.000

Twin castors


State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

CP 7495.000 - Twin castors

For mobile use, can be mounted directly on the enclosure.







Features

Model No.	CP 7495.000
Product description	For mobile use, can be mounted directly on the enclosure.
Color	Black
Supply includes	4 twin castors, 2 x with, 2 x without locks. Assembly components
Note on Model No.:	When mounting on a VX base/plinth, the base/plinth adapter is required When mounting on a TS base/plinth, the base/plinth adapter is required
Suitable for	Enclosure type: VX Enclosure type: VX IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Blue e+ chiller Enclosure type: VX25 TopTherm chiller
Clearande floor	125 mm 4.92 ″

© Rittal 2026

Features

Max. load capacity (static) per component	1,200 N 269.771 lbf.
Dimensions	Thread: M12 x 20
Packaging unit	4 pc(s).
Net weight	1.76 kg
Gross weight	1.98 kg
Customs tariff number	83024900
ETIM 9	EC002621
ECLASS 8.0	27189262
Product description	DK Twin castors, M12, each 2 with/without Lock