

Rittal – The System.

Faster – better – everywhere.



DK 7501.000 VerticalBox

State: 8/17/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7501.000 - VerticalBox

Compact 19" enclosure for small networks that may be used for wall-mounted, under-desk or desktop applications.



Features

Model No.	DK 7501.000
Product description	Compact 19" enclosure for small networks.
Benefits	May be used as wall-mounted, under-desk or desktop applications Free access from three sides for interior installation Passive ventilation with vent slots Rear panel prepared to accommodate a fan Freely selectable door catch Space-saving, vertical mounting of 19" installation components at the side
Material	Carbon steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

Features

Supply includes	Housing with viewing door Side panels (1 x fixed, 1 x slot-in) with vent slots Knockouts for cable entry via roof or base Slot-in rear panel with knockouts for cable entry and fan accommodation 19" mounting level, 5 U, horizontal front and rear, depth-variable, distance between levels 434 – 489 mm Security lock 12321 on the door, side and rear panel 4 plastic feet, self-adhesive
Height units	5 U
Dimensions	Width: 300 mm Height: 540 mm Depth: 600 mm Width: 11.8 " Height: 21.3 " Depth: 23.6 "
Installation height for components	5 U
Base material	Carbon steel
Load capacity	250 N
Max. load capacity (static) per cabinet according to UL 2416	250 N
Packaging unit	1 pc(s).
Net weight	16.188
Gross weight	17.04
PCF/VE (cradle-to-gate)	64.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177625426
ETIM 9	EC002500
ECLASS 8.0	27180208

Approvals

Explanations

Manufacturer's declaration