

Rittal – The System.

Faster – better – everywhere.



VX 8100.700 Transport castors

State: 4/28/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8100.700 - Transport castors For VX base/plinth systems

For fitting on the base/plinth corner piece, height 100 or 200 mm.

Features

Model No.	VX 8100.700
Product description	Locate onto the base/plinth corner piece, height 100 or 200 mm.
Color	RAL 9005
Supply includes	4 twin castors, 2 x with, 2 x without locks.
Clearance floor	100 mm 3.94 "
Load capacity	Max. dynamic load when using 4 double castors (single enclosure): 3000 N
Weight/packaging unit	8.38 kg 18.5 lb.
Packaging unit	4 pc(s).
Net weight	7.98 kg
Gross weight	8.38 kg
Customs tariff number	83024900
ETIM 9	EC002621
ETIM 8	EC002621
ECLASS 8.0	27189262
Product description	VX Transport castors, 2 each with/without lock