


Rittal – The System.

Faster – better – everywhere.



VX 8205.000

Baying-enclosure system VX25

State: 9/27/2026 (Source: www.rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8205.000 - Baying-enclosure system VX25 Basic enclosure

The standard in enclosure assembly: enclosure frame with two front doors, rear panel, mounting plate, roof plate, divided base plates. Perfectly suited for efficient enclosure assembly.



Features

Model No.	VX 8205.000
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Base plates: Carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035

Features

Supply includes	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Roof plate Rear panel Base Plates Mounting panel 2 punched rails, 18 x 39 mm Lock: 3 mm double-bit
Dimensions	Width: 1,200 mm Height: 2,000 mm Depth: 500 mm Width: 47.2 " Height: 78.7 " Depth: 19.7 "
Dimensions of mounting plate (W x H)	1,099 mm x 1,896 mm 43.3 " x 74.6 "
Protection category IP to EN 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Type rating according to UL 50E	Type 1 Type 12
IK code	IK10
Number of doors	2
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	173.61 kg
Gross weight	186.8 kg
PCF/VE (cradle-to-gate)	486.32 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080

Features

ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	VX Baying enclosure system, WHD: 1200x2000x500 mm, sheet steel, with mounting plate, two doors at the front

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity PCF-declaration