

# Rittal – The System.

Faster – better – everywhere.



## DK 7507.110 FlatBox

State: 5/11/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7507.110 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.



## Features

Model No.	DK 7507.110
Version	with 19" mounting rails
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting System accessories on the open 19" frame
Material	Carbon steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

# Features

Supply includes	Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts 19" profile rails
Height units	9 U
Dimensions	Width: 600 mm Height: 492 mm Depth: 600 mm Width: 23.6 " Height: 19.4 " Depth: 23.6 "
Installation height for components	9 U
Load capacity	max. 450 N
Note	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210°
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	24.42 kg
Gross weight	26.3 kg
PCF/VE (cradle-to-gate)	102.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC002500
ETIM 8	EC002500

# Features

---

ECLASS 8.0

27180208

---

Product description

DK FlatBox, WHD: 600x492x600 mm, 9 U, with 482.6 mm (19")  
mounting angles

# Approvals

---

Explanations

Manufacturer's declaration