Rittal - The System.

Faster – better – everywhere.





DK 7507.120 FlatBox

State: 11/19/2025 (Source: rittal.com/us-en)



DK 7507.120 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.







Features

Model No.	DK 7507.120
Version	with 19" mounting frame
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting
	System accessories on the open 19" frame
Material	Carbon steel
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

© Rittal 2025

Features

Supply includes	Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts
Height units	19" mounting frame 12 U
Dimensions	Width: 600 mm Height: 625 mm Depth: 600 mm Width: 23.6 " Height: 24.6 " Depth: 23.6 "
Installation height for components	12 U
Load capacity	max. 600 N
Note	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210°
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	29.45
Gross weight	30.18
PCF/VE (cradle-to-gate)	118.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177551459
E-Number Sweden	E7238405

© Rittal 2025

3

Features

ETIM 9	EC002500	
ETIM 8	EC002500	
ECLASS 8.0	27180208	

Approvals

Explanations Manufacturer's declaration

© Rittal 2025