

Rittal – The System.

Faster – better – everywhere.



TS 8454.600

Baying systems TS 8

State: 9/6/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8454.600 - Baying systems TS 8 Stainless steel

TS 8 stainless-steel baying systems 1.4301, (AISI 304), incl. mounting plate. Protection category IP 55.



Features

Model No.	TS 8454.600
Material	Enclosure frame: Stainless steel 1.4301 (AISI 304), 1.5 mm Roof: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Door: Stainless steel 1.4301 (AISI 304), 2.0 mm, exterior brushed Rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Base plates: Stainless steel 1.4301 (AISI 304), 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame and base plates: Uncoated Door, roof and rear panel: Exterior brushed, grain size 400 Mounting panel: Zinc-plated
Supply includes	Enclosure frame Door(s) Right-hand door catch on single-door enclosures may be swapped to the left Roof plate Base Plates Rear panel Mounting panel 4 eyebolts Lock: 3 mm double-bit 2 TS punched rails, 18 x 38 mm
Number of doors	1

Features

Protection category IP to IEC 60529	IP 55
Type rating according to UL 50E	Type 1 Type 12
Protection category NEMA	NEMA 1 NEMA 12
IK code	IK09
Note	Due to the hardness of the material, we recommend using metal multi-tooth screws for the interior installation.
Base material	Stainless steel
Dimensions	Width: 800 mm Height: 1,800 mm Depth: 400 mm Width: 31.5 " Height: 70.9 " Depth: 15.7 "
Dimensions of mounting plate (W x H)	699 mm x 1,696 mm 27.5 " x 66.8 "
Packaging unit	1 pc(s).
Net weight	106.1
Gross weight	112.9
EAN	4028177300750
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK