## Rittal - The System.

Faster – better – everywhere.





# DK 7507.200 FlatBox

State: 12/8/2025 (Source: rittal.com/us-en)



#### DK 7507.200 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.







#### **Features**

Model No.	DK 7507.200
Version	with 19" mounting frame
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting
	System accessories on the open 19" frame
Material	Carbon steel
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035

© Rittal 2025

#### **Features**

Supply includes	Flat-packed enclosure		
	1 wall section		
	2 basic supports		
	2 roof/base plates, with cut-outs for cable entry via brush strips		
	2 side panels, lockable		
	1 glazed door, lockable, security lock 3524 E, door catch freely selectable		
	Connection components for tool-free, fast assembly		
	Grounding kit for system-compatible grounding of all enclosure		
	parts		
	19" mounting frame		
Height units	15 U		
Dimensions	Width: 700 mm		
	Height: 758 mm		
	Depth: 700 mm		
	Width: 27.6 "		
	Height: 29.8 "		
	Depth: 27.6 "		
Installation height for components	15 U		
Load capacity	max. 750 N		
Note	Max. installation depth: Depth - 58 mm to rear panel		
	Max. distance between two 19" levels: Depth - 104 mm		
	The door opening angle is max. 210°		
Base material	Carbon steel		
Packaging unit	1 pc(s).		
Net weight	39.9		
Gross weight	41.8		
PCF/VE (cradle-to-gate)	160 kg CO2 eq (Cat B)		
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared		
Customs tariff number	94032080		
EAN	4028177551466		
E-Number Sweden	E7238406		

© Rittal 2025

3

### **Features**

ETIM 9	EC002500	
ETIM 8	EC002500	
ECLASS 8.0	27180208	

## **Approvals**

Explanations Manufacturer's declaration

© Rittal 2025