
Rittal – The System.

Faster – better – everywhere.



# TS 8601.080

# Base/plinth trim panels, side, 100 mm

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 8601.080 - Base/plinth trim panels, side, 100 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used. Base/Plinth panels can be installed turned at 90° to provide stabilization for bayed base/plinth components.

## Features

| | |
|---|---|
| Model No. | TS 8601.080 |
| Product description | To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 7022 |
| Supply includes | 2 plinth/base trim panels<br>Assembly components |
| Mounting tip | 100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here |
| Dimensions | Height: 100 mm<br>Height: 3.94 ˝ |

© Rittal 2026

# Features

| | |
|---|---|
| Suitable for | Enclosure type: TS: = 800 mm<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT<br>Enclosure type: TS: = 31.5 ″<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT |
| Packaging unit | 2 pc(s). |
| Net weight | 2.66 kg |
| Gross weight | 2.86 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182003 |
| Product description | TS Trim panel, sides, H: 100 mm, for W: 800 mm, RAL 7022, sheet steel |

© Rittal 2026