Rittal – The System.

Faster – better – everywhere.



TS 8609.080

Divider panel

State: 11/11/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8609.080 - Divider panel for TS

To shield individual enclosure cells. The symmetry of the frame system means the divider panel can also be used at the rear.



Features

Model No.	TS 8609.080
Product description	To shield individual enclosure cells. All-round, double edging for stability and to accommodate the seal. The symmetry of the enclosure frame means divider panels of the appropriate dimensions can also be fitted at the rear.
Applications	Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted.
Material	Carbon steel, 1.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly components
Suitable for	Enclosure type: TS 8 Height: = 2,000 mm Depth: = 800 mm Enclosure type: TS 8 Height: = 78.7 ″ Depth: = 31.5 ″
Installation options	Mounted on the outer mounting level The inner level remains free for further expansion

© Rittal 2026

Features

Mounting tip	The divider panel may also be fitted at the rear. This allows, e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/ concealed with a cover.
Protection category IP to IEC 60 529	IP 54
Packaging unit	1 pc(s).
Net weight	17.683 kg
Gross weight	18.61 kg
Customs tariff number	94039910
ETIM 9	EC002525
ECLASS 8.0	27182102
Product description	TS Divider panel, for TS, for WD: 2000x800 mm

© Rittal 2026