

Rittal – The System.

Faster – better – everywhere.



TS 8612.030

TS System Chassis 17 x 73 mm

State: 2/10/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

TS 8612.030 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

Model No.	TS 8612.030
Version	For the inner mounting level and for mounting on doors
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	290 mm 11.4 "
Suitable for door width	400 mm 15.7 "
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

Features

Suitable for	Enclosure type: VX SE TP PC IW Width/depth: 300 mm
	Enclosure type: VX SE TP PC IW Width/depth: 11.8 "
Packaging unit	4 pc(s).
Net weight	1.2
Gross weight	1.32
PCF/VE (cradle-to-gate)	5.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177611504
ETIM 9	EC002625
ECLASS 8.0	27189234