Rittal – The System.

Faster - better - everywhere.





TS 8612.040 TS System Chassis 17 x 73 mm

State: 10/29/2025 (Source: rittal.com/us-en)




TS 8612.040 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.







Features

TS 8612.040 For the inner mounting level and for mounting on doors For universal skeleton structures or partial assembly. Simply locate
For universal skeleton structures or partial assembly. Simply locate
onto the punchings and secure.
Carbon steel
Zinc-plated
Assembly screws
390 mm 15.4 ″
500 mm 19.7 ″
On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset
On the horizontal VX SE enclosure section top, in depth
In TP via rails for interior installation: in width, for inner mounting level
As installation kit for device bases in TS, VX SE, simply hook in and secure
The rail for interior installation is required when installing in TP

© Rittal 2025

Features

Suitable for	Enclosure type: VX SE
	TP
	PC
	IW
	Suitable for width/depth: 400 mm
	Enclosure type: VX SE
	TP
	PC
	IW
	Suitable for width/depth: 15.7 "
Packaging unit	4 pc(s).
Net weight	1.6
Gross weight	1.75
PCF/VE (cradle-to-gate)	6.7 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177212077
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3