

**Rittal – The System.**

Faster – better – everywhere.



**DK 7825.380**

**Base plate modules, vented**

State: 5/23/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7825.380 - Base plate modules, vented for TS IT, TS, SE, TX CableNet

Base plate module, vented for TS, TS IT, SE, for use in network enclosure base frames. To replace an existing base plate of the same depth.

## Features

Model No.	DK 7825.380
Product description	Large perforated section for passive enclosure ventilation.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Incl. filter mat and Velcro strap
Note	Several base plate modules need to be combined to close off the base completely in the TS-IT
Dimensions	Depth: 237.5 mm Depth: 9.35 "
Suitable for	Enclosure type: TS TS IT SE TX CableNet Width: 800 mm Enclosure type: TS TS IT SE TX CableNet Width: 31.5 "
Packaging unit	1 pc(s).
Net weight	1.95 kg
Gross weight	2.26 kg
PCF/VE (cradle-to-gate)	8.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

# Features

---

Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK base plate module, ventilated, depth: 237.5 mm, for enclosure width: 800 mm, for TS, TS IT, SE, TX CableNet, carbon steel, zinc-plated