
Rittal – The System.

Faster – better – everywhere.



# TS 7825.387

# Base modules for cable entry

State: 11/11/2026 (Source: www.rittal.com/us-en)

ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 7825.387 - Base modules for cable entry for TS, TS IT, VX SE

The two-part base module has a special cable entry with alternate offset brush strips, providing an excellent seal even with large numbers of cables.



## Features

| | |
|---|---|
| Model No. | TS 7825.387 |
| Version | Cable entry with brush strip, super-airtight |
| Product description | Special brush strips with alternate offset brushes for optimum protection of correct cable entry. The two-piece design even allows retrospective fitting of the base module with the cables already installed. |
| Material | Module plate: Carbon steel<br>Brush strip: Plastic, UL 94-HB, halogen-free |
| Surface finish | Module plate: Zinc-plated |
| Supply includes | Assembly components<br>Including clips |
| Note | Several base plate modules need to be combined to close off the base completely in the TS-IT |
| Dimensions | Depth: 237.5 mm<br>Depth: 9.35 ″ |

© Rittal 2026

# Features

| | |
|---|---|
| Suitable for | Enclosure type: TS<br>TS IT<br>SE<br>Width: 800 mm<br>Enclosure type: TS<br>TS IT<br>SE<br>Width: 31.5 ˝ |
| Packaging unit | 1 pc(s). |
| Net weight | 1.811 kg |
| Gross weight | 1.9 kg |
| Customs tariff number | 83024200 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Gland plate module, For W: 800 mm, For cable entry with brush, super-airtight |