Rittal – The System.

Faster – better – everywhere.




TS 8612.090


TS System Chassis 17 x 73 mm

State: 11/10/2026 (Source: www.rittal.com/us-en)

TS 8612.090 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.





Features

Model No.	TS 8612.090
Version	For mounting on doors
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	890 mm 35 ″
Suitable for door width	1,000 mm 39.4 ″
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

Features

Suitable for	Enclosure type: VX SE TP PC IW
Packaging unit	4 pc(s).
Net weight	3.3 kg
Customs tariff number	73269098
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	TS punched section with mounting flange, 17 x 73 mm, for door width: 1000 mm, L: 890 mm

© Rittal 2026