Rittal - The System.

Faster - better - everywhere.





TS 8612.100 TS System Chassis 17 x 73 mm

State: 11/24/2025 (Source: rittal.com/us-en)



TS 8612.100 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

Model No.	TS 8612.100
Version	For the outer mounting level
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	940 mm 37 ″
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset
	On the horizontal VX SE enclosure section top, in depth
	In TP via rails for interior installation: in width, for inner mounting level
	As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

© Rittal 2025

Features

Suitable for	Enclosure type: VX SE
	TP
	PC
	IW
	TX CableNet
	Suitable for width/depth: 1,000 mm
	Enclosure type: VX SE
	TP
	PC
	IW
	TX CableNet
	Suitable for width/depth: 39.4 ″
Packaging unit	4 pc(s).
Net weight	3.956
Gross weight	4.26
PCF/VE (cradle-to-gate)	16.4 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177212114
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3