

Rittal – The System.

Faster – better – everywhere.



TS 8612.100

TS System Chassis 17 x 73 mm

State: 4/22/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.100 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

Model No.	TS 8612.100
Version	For the outer mounting level
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	940 mm 37 "
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset On the horizontal VX SE enclosure section top, in depth In TP via rails for interior installation: in width, for inner mounting level As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

Features

Suitable for	Enclosure type: VX SE TP PC IW TX CableNet Width/depth: 1,000 mm Enclosure type: VX SE TP PC IW TX CableNet Width/depth: 39.4 ~
Packaging unit	4 pc(s).
Net weight	3.956 kg
Gross weight	4.26 kg
PCF/VE (cradle-to-gate)	16.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	TS punched section with mounting flange, 17 x 73 mm, for outer mounting level: W/D: 1000 mm, L: 940 mm