Rittal – The System.

Faster - better - everywhere.





TS 8612.140 TS System Chassis 17 x 73 mm

State: 12/11/2025 (Source: rittal.com/us-en)



TS 8612.140 - TS System Chassis 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.







Features

Model No.	TS 8612.140
Version	For the outer mounting level
Product description	For universal skeleton structures or partial assembly. Simply locate onto the punchings and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	340 mm 13.4 ″
Installation options	On the vertical TS, VX SE enclosure profile: on the inner mounting level, all-round, height-offset
	On the horizontal VX SE enclosure section top, in depth
	In TP via rails for interior installation: in width, for inner mounting level
	As installation kit for device bases in TS, VX SE, simply hook in and secure
Mounting tip	The rail for interior installation is required when installing in TP

© Rittal 2025

Features

Enclosure type: VX SE TP
PC
IW
Width/depth: 400 mm
Enclosure type: VX SE
TP
PC
IW
Width/depth: 15.7 "
4 pc(s).
1.4
1.46
6.1 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
73269098
4028177212138
EC002625
27189234

© Rittal 2025 3