

Rittal – The System.

Faster – better – everywhere.



TE 7888.510

Network enclosure TE 8000

State: 4/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7888.510 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

Features

| | |
|-----------------|---|
| Model No. | TE 7888.510 |
| Version | with side panels |
| Benefits | No frame structure Optimum accessibility Easily installed Interchangeable door catch |
| Material | Carbon steel Viewing door: Single-pane safety glass, 3 mm |
| Surface finish | Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated |
| General color | RAL 7035 |
| Color | RAL 7035 |
| Supply includes | Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Side panels, lockable, including security lock 3524 E |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 " Height: 78.7 " Depth: 31.5 " |

Features

| | |
|---|---|
| Height units | 42 U |
| Height units | 42 U |
| Mounting space to 19" level, front/ rear | 130 mm / 130 mm / |
| Distance between levels as delivered | 495 mm 19.5 " |
| Load capacity | 4,000 N |
| Protection category IP to EN 60 529 | IP 20 |
| Base material | Carbon steel |
| Packaging unit | 1 pc(s). |
| Net weight | 88.5 kg |
| Gross weight | 96.5 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002499 |
| ECLASS 8.0 | 27180207 |
| Product description | TE Network enclosure TE 8000, WHD: 600x2000x800 mm, 42 U, With glazed door |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|