

**Rittal – The System.**

Faster – better – everywhere.



**DK 7955.911**

**Slave PDU international, managed  
version**

State: 4/5/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7955.911 - Slave PDU international, managed version

Slave PDU for connection to the PDU Master, metered, switched and managed versions and the CMC III. Measurement and switching functionality as on PDU managed, but without integral display and network interface/web interface. The PDU Master or CMC III is essential for operation. A maximum of 3 slave PDUs can be connected for each CAN bus.

## Features

Model No.	DK 7955.911
Product description	Up to three slave PDUs can be connected to one PDU managed. Thanks to the compact PDU, all IT racks can easily be equipped with a professional power distribution system. In the case of the TS IT rack, mounting is even possible without tools. The compact design enables easy mounting. Due to the installation of bistable relays the PDU has low energy consumption. The redundant power supply originates from all phases. The PDU offers extensive management and monitoring functions. High reliability is guaranteed thanks to +/- 1% measurement accuracy.
Material	Aluminum section, black anodized
Dimensions	Width: 44 mm Depth: 85 mm Length: 1,360 mm Width: 1.73 " Depth: 3.35 " Length: 53.5 "
Number of sockets and type	24 x C13 / 4 x C19
Outlets	24 x Non-Heating Apparatus Socket C13 4 x Non-Heating Apparatus Socket C19
Rated current (max.)	32 A
Infeeds	Qty.: 1 Phases per infeed: 1~
Length of connection cable	3 m 118 "
Type of connection (electrical)	CEE

# Features

Number RJ45 ports for sensor units max	2
Guidelines	EMC Directive 2014/30/EU Low-Voltage Directive 2014/35/EU
Standards	EN 60950-1
Operating temperature range	0 °C...45 °C 32 °F...113 °F
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Suitable for	Enclosure type: TS IT: ≤ 1,800 mm Enclosure type: TS IT: ≤ 70.9 "
Packaging unit	1 pc(s).
Net weight	6 kg
Gross weight	7 kg
Customs tariff number	85366990
ETIM 9	EC002762
ECLASS 8.0	27142604
Product description	DK Slave PDU international, managed version, Connecting up to 3 Slave PDU to PDU managed, WLD: 44x1360x85 mm, 24xC13, 4xC19, black, CEE, 1~, 32 A