

Rittal – The System.

Faster – better – everywhere.



DK 7966.035

Fan tray

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7966.035 - Fan tray

Can be retro-fitted from above in all TS 8 network enclosures. The rear section is left free for cable entry. Two fans as standard. Can be increased to max. 4/6 fans.

Features

| | |
|---------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | DK 7966.035 |
| Product description | For upgrading existing DK-TS applications. The plate is mounted at the front of the enclosure, while the rear section is left free for cable entry. A rubber sealing profile is included for optional sealing at the rear. |
| Color | RAL 7035 |
| Supply includes | Fan plate including 2 fans and extra cut-outs for additional fans 1 thermostat Self-adhesive foam cable clamp strip Thermostat and fan fully wired to connection cable (3.5 m). |
| Air throughput per fan (unimpeded air flow) | 160/180 94.2/105.9 |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Air throughput of fans (unimpeded air flow) | 1514 |
| Installation options | In a solid roof plate raised with 20 or 50 mm roof spacers In a roof plate for cable entry raised with 20 or 50 mm roof spacers In a vented roof plate for cable entry |
| Mounting tip | Self-adhesive foam cable clamp strip 2573.000 is required for sealing the sides and for targeted air routing when bayed |
| Note | Not suitable for crane transportation In conjunction with the large pivoting frame or the roof plate for cable entry at the rear, the fan mounting plate should be selected as follows: Fan mounting plate = enclosure depth – 200 mm Cannot be used in combination with 482.6 mm (19") mounting frame Air throughput can be increased with fan expansion kit 7980.000. The specified sound level relates to the first fan |

Features

| | |
|------------------------------|-------------------------------------------------------------------------|
| Sound pressure level per fan | 37 dB(A) |
| Suitable for | Width: 600 mm Depth: 600 mm Width: 23.6 " Depth: 23.6 " |
| Operating temperature range | 5 °C...55 °C 41 °F...131 °F |
| Packaging unit | 1 pc(s). |
| Net weight | 3.864 kg |
| Gross weight | 4.064 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000331 |
| ECLASS 8.0 | 27189272 |
| Product description | DK Fan mounting plate, WxD: 600x600 mm, 230 V, 1 ~, 50/60 Hz, For TS |