


Rittal – The System.

Faster – better – everywhere.



VX 8617.200

System chassis 23 x 64 mm

State: 6/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8617.200 - System chassis 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable and individual interior fitting of the enclosure frame on the inner mounting level and for installation in compact control enclosures.



Features

| | |
|----------------------------|--|
| Model No. | VX 8617.200 |
| Product description | For variable and individual interior fitting of the enclosure frame on the inner mounting level and for installation in compact control enclosures. |
| Benefits | Simply place in the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options VX | In enclosure height 2000 mm, on the inner mounting level |
| Installation options VX SE | In enclosure height 2000 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility |

Features

| | |
|-------------------------|---|
| Suitable for | Enclosure type: VX VX IT VX SE Suitable for width or height or depth: 2,000 mm |
| Packaging unit | 4 pc(s). |
| Net weight | 7.56 kg |
| Gross weight | 8.62 kg |
| PCF/VE (cradle-to-gate) | 44.86 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level |

Approvals

| | |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|