

**Rittal – The System.**

Faster – better – everywhere.



**VX 8617.351**

**Mounting plate attachment**

State: 6/15/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.351 - Mounting plate attachment Type B, for VX

For additional clamping and to reduce potential vibration of the mounting plate.



## Features

|                         |   |
|-------------------------|---|
| Model No.               | VX 8617.351   |
| Product description     | For additional clamping and to reduce potential vibration of the mounting plate.  |
| Benefits                | Easy mounting directly on the enclosure frame or on the 23 x 64 mm system chassis   |
| Function principle      | The mounting plate can either be firmly screwed onto the mounting plate fixture or inserted so that it interlocks<br>The type B mounting plate fixture may slightly surround the mounting plate, depending on the installation situation<br>Keeps the front of the mounting plate completely free for unrestricted use<br>Attachment is possible from the front or the rear, depending on the situation |
| Material                | Carbon steel  |
| Surface finish          | Zinc plated, clear-chromated  |
| Supply includes         | Assembly components   |
| Packaging unit          | 10 pc(s).   |
| Net weight              | 1.34 kg   |
| Gross weight            | 1.44 kg   |
| PCF/VE (cradle-to-gate) | 5.8 kg CO2 eq (Cat B)   |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number               | 73269098   |
| ETIM 9                              | EC002620   |
| ECLASS 8.0                          | 27189261   |
| Product description                 | VX Mounting plate attachment, type B, sheet steel  |

---